


TOL ±								
	MI	M2	SI	S2	PI	P2	C	URS
RANGE								
0~6	0.05	0.10	0.15	0.20	0.05	0.10	0.50	
6~30	0.10	0.20	0.15	0.25	0.10	0.15	1.00	
30~120	0.15	0.25	0.20	0.30	0.20	0.40	2.00	
120~300	0.15	0.30	0.25	0.45	0.40	0.80	3.00	
300~600	0.20	0.50	0.40	0.60	0.60	1.20	3.00	
600~1200	0.30	0.80	0.70	1.10	0.80	1.50	4.00	
ANG. TOL±	1°							

MODEL		Lightning		NAME			Re-Timer Bracket					
DRN	William Aj Lin	11/27/2015	MATERIAL	SGCC	t=1mm	REV	DESCRIPTION			SIGN	DATE	
DSN	William Aj Lin	11/27/2015	FINISH	N/A				DIM IN	mm	DO NOT SCALE DWG		
CKD		11/27/2015	Wiwynn Corporation			SHEET		1	OF	1		
APPD		11/27/2015				DRAWING NO.			CD B33.00Q08.0001			