



Convertible Rack

StackVelocity™ is...



...a business unit within Jabil providing cloud hardware and software systems integration at global scale.

Our rack-level integrated solutions are designed for customers with specific needs where open source software and cost-optimized hardware are required.



**EIA and OCP Configuration
In a single rack**



Rack Features

- Can be shipped “flat”
- Static load capacity up to 1500kg
- Cable entry via base and roof (optional)
- Doors and sides are optional and lockable
- Doors are reversible without machining
- Full or split door options
- Top panels are available in a variety of configurations



Basic Rack Dimensions




| Standard Rack | |
|-------------------------|----------------------|
| Width | 712mm (28 inches) |
| Depth (W/O Doors) | 1220mm (48 inches) |
| Depth (W/ Doors) | 1291mm (50.9 inches) |
| Height (Inches) | 2312mm (91 inches) |
| Height (EIA Rack Units) | 48u |
| Height (OCP Rack Units) | 44ou |



| Short Rack | |
|-------------------------|----------------------|
| Width | 712mm (28 inches) |
| Depth (W/O Doors) | 1220mm (48 inches) |
| Depth (W/ Doors) | 1291mm (50.9 inches) |
| Height (Inches) | 2109mm (83 inches) |
| Height (EIA Rack Units) | 44u |
| Height (OCP Rack Units) | 40ou |

Total Assembly


STACK[®]
VELOCITY



Internal Components




Power Shelf Support
(L/R pair) 30U



Knife Base
(L/R pair) 20U

Exterior Components





Contact us to learn more:
info@stackvelocity.com