


REVISIONS						
REV.	DESCRIPTION	MOD BY	MOD DATE	APPROVED	APPROVED DATE	
01	INITIAL RELEASE					



1. DIMENSION ARE IN MILLIMETERS
2. MATERIAL: 0.8mm CRS
3. TOLERANCE UNLESS OTHERWISE SPECIFIED: ± 0.25mm, MAX BEND RADIUS 0.30mm
4. THE FOLLOWING DIMENSIONS MUST MEET A Cp>=1.33 and Cpk>=1.00
5. BEND RELIEFS ALLOWED. FACEPLATE GEOMETRY MUST BE MAINTAINED.
6. PARTS MUST COMPLY WITH RoHS DIRECTIVE 2002/95/EC. FURTHERMORE, THE USE OF HEXAVALENT CHROMIUM IN THE FABRICATION PROCESS IS NOT ALLOWED.

UNLESS OTHERWISE SPECIFIED:		SIGNATURE		DATE		OPEN	
1. DIMENSIONS ARE IN: MILLIMETER		DRAWN BY: J. MAI		6/05/2019		TITLE:	
2. DO NOT SCALE DRAWING.		CHECKED BY: J. HELD		6/05/2019		DOCUMENT NUMBER	
3. TOLERANCES:		APVD:				NIC_OCPv3_SFF_Faceplate_Latch_20190605	
ANGLES: X ± 1.0° XX ± 0.25		THIRD ANGLE PROJECTION				SIZE: D	
						SCALE: 3:1	
						SHEET: 1 OF 1	
						REV: 01	

