






REVISIONS						
REV.	DESCRIPTION	MOD BY	MOD DATE	APPROVED	APPROVED DATE	
01	INITIAL RELEASE					



1. DIMENSION ARE IN MILLIMETERS
2. MATERIAL: 0.8mm CRS
3. TOLERANCE UNLESS OTHERWISE SPECIFIED: ±0.25mm, MAX BEND RADIUS 0.30mm
4. THE FOLLOWING DIMENSIONS MUST MEET A Cp>=1.33 and CpK>=1.00
5. BEND RELIEFS ALLOWED. FACEPLATE GEOMETRY MUST BE MAINTAINED.
6. PARTS MUST COMPLY WITH RoHS DIRECTIVE 2002/95/EC. FURTHERMORE, THE USE OF HEXAVALENT CHROMIUM IN THE FABRICATION PROCESS IS NOT ALLOWED.

UNLESS OTHERWISE SPECIFIED:  
1. DIMENSIONS ARE IN:  
MILLIMETER  
2. DO NOT SCALE DRAWING.  
3. TOLERANCES:  
ANGLES ± 1.0°  
XX ± 0.25

SIGNATURE	DATE
DRAWN BY: J. MAI	6/05/2019
CHECKED BY: J. HELD	6/05/2019
ENGR	
APVD:	
THIRD ANGLE PROJECTION	

OPEN

TITLE:

DOCUMENT NUMBER

NIC\_OCPv3\_SFF\_Faceplate\_Pulltab\_20190605

SIZE

SCALE

3:1

SHEET

1 OF 1

REV

01