



OPEN

Compute Project

Open Rack V3 Power Output Connector

Rev: 1.4

Author

Skip Fry

Amphenol

License OCP CLA Option

Contributions to this Specification are made under the terms and conditions set forth in Open Compute Project Contribution License Agreement (“OCP CLA”) (“Contribution License”) by:

[Contributor Name(s) or Company name(s)]

You can review the signed copies of the applicable Contributor License(s) for this Specification on the OCP website at <http://www.opencompute.org/products/specsanddesign>

Usage of this Specification is governed by the terms and conditions set forth in Open Web Foundation Final Specification Agreement (“OWFa 1.0”).

You can review the applicable Specification License(s) executed by the above referenced contributors to this Specification on the OCP website at <http://www.opencompute.org/participate/legal-documents/>

Note: The following clarifications, which distinguish technology licensed in the Contribution License and/or Specification License from those technologies merely referenced (but not licensed), were accepted by the Incubation Committee of the OCP:

[insert “None” or a description of the applicable clarifications].

NOTWITHSTANDING THE FOREGOING LICENSES, THIS SPECIFICATION IS PROVIDED BY OCP “AS IS” AND OCP EXPRESSLY DISCLAIMS ANY WARRANTIES (EXPRESS, IMPLIED, OR OTHERWISE), INCLUDING IMPLIED WARRANTIES OF MERCHANTABILITY, NON-INFRINGEMENT, FITNESS FOR A PARTICULAR PURPOSE, OR TITLE, RELATED TO THE SPECIFICATION. NOTICE IS HEREBY GIVEN, THAT OTHER RIGHTS NOT GRANTED AS SET FORTH ABOVE, INCLUDING WITHOUT LIMITATION, RIGHTS OF THIRD PARTIES WHO DID NOT EXECUTE THE ABOVE LICENSES, MAY BE IMPLICATED BY THE IMPLEMENTATION OF OR COMPLIANCE WITH THIS SPECIFICATION. OCP IS NOT RESPONSIBLE FOR IDENTIFYING RIGHTS FOR WHICH A LICENSE MAY BE REQUIRED IN ORDER TO IMPLEMENT THIS SPECIFICATION. THE ENTIRE RISK AS TO IMPLEMENTING OR OTHERWISE USING THE SPECIFICATION IS ASSUMED BY YOU. IN NO EVENT WILL OCP BE LIABLE TO YOU FOR ANY MONETARY DAMAGES WITH RESPECT TO ANY CLAIMS RELATED TO, OR ARISING OUT OF YOUR USE OF THIS SPECIFICATION, INCLUDING BUT NOT LIMITED TO ANY LIABILITY FOR LOST PROFITS OR ANY CONSEQUENTIAL, INCIDENTAL, INDIRECT, SPECIAL OR PUNITIVE DAMAGES OF ANY CHARACTER FROM ANY CAUSES OF ACTION OF ANY KIND WITH RESPECT TO THIS SPECIFICATION, WHETHER BASED ON BREACH OF CONTRACT, TORT (INCLUDING NEGLIGENCE), OR OTHERWISE, AND EVEN IF OCP HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Table of Contents

1. Scope	3
2. Overview	3
3. Electrical	3
4. Environmental	3
5. Mechanical	4
5.1 Geometry	4
5.2 Mating to the ORv3 Busbar	5
6. Quality	6
7. Regulatory	8
8. Ordering Part Numbers	8
9. Revisions	8

1. Scope

This document defines the technical specifications for an Open Rack V3 Power Output Connector used in the Open Compute Project.

2. Overview

This interconnection is the power interface between Open Rack V3 Power shelves (PSU Shelf and BBU Shelf) and the Open Rack V3 48V bus bar.




Figure 1: 10U Power Shelf and ORv3 Busbar
(Optional chassis ground contacts not shown)

3. Electrical

- Voltage range: 46.0V – 52.0V DC
- Power Contact Max current continuous in still air: 360A
- Power Contact Max current continuous in 300LFM @ 45°C airflow: 500A
- Max temperature rise: 30°C (with busbar connected, as specified in ORv3 Busbar Spec)
- Power Contact Max voltage drop: 14mV @ 360A, 20mV @ 500A
- Chassis Ground Contact Max Current for 2-minute duration in still air: 64A total (2 contacts x 32A)
 - Chassis Ground Contacts may not be required for some applications.
- This connector is not designed for hot plug/unplug applications (no mate/break under load).



4. Environmental

- Operating Ambient Temperature at connector location: 15°C to 70°C
- Long-term Storage: -40C to 50C and 5-95% RH
- Short-term Storage: -20C to 65C and 10-80% RH
- Operating Humidity: 20-90%, 5C dew point minimum
- Lifetime: 5 years

5. Mechanical

5.1 Geometry

- The connector shall fit within the maximum height of 1 Open Rack Unit (48.00mm) including $\pm 3.0\text{mm}$ vertical connector float (as defined in section 4.2).
- Wires shall resist pullout from the connector of 15kgf.
- The connector shall support a panel thickness of 1.10 to 1.32 mm.
- Tools may be required to attach the connector to the shelf.
- Torque range for applicable mounting hardware shall be 0.7 - 0.9 NM.
- The connector is not intended to control the location of the power shelf in the rack (not for use as a mechanical stop).



5.2 Mating to the ORv3 Busbar

- The ORv3 48V Busbar is defined in the Open Rack Standard V3.0 specification. The busbar details shown below are provided for reference only.




Figure 2: ORv3 Busbar Mechanical Detail (reference only)

- All busbar contact points shall be silver plated.
- The connector shall support blind-mate installation of the Power Shelf connector onto the ORv3 busbar (figure 4) as defined in the Open Compute Specification Revision 3.0.
- Connector shall support +/-3mm float horizontally and vertically.
- Connector shall enable 6.4mm side-to-side gatherability.
- The max rate of the power shelf insertion into the rack will be 1 m/s.
- The mating force of the connector with the busbar shall be less than 120N.
- The power shelf will ship within the rack while connected to the rack busbar. The connector solution shall prevent damage of the power shelf and the rack busbar during the following packaged, rack-level tests (ASTM 4169 details below) while meeting the voltage drop requirements per section 6.0 and show no exposed copper of either the power shelf connector or rack busbar under SEM analysis of the interfaces.
- The rack is tested in the shipping packaging for transportation Shock and Vibration per ASTM 4169-16 Schedule E - Vehicle Vibration for 2hrs on vertical axis only for 80 minutes low level, 30 minutes medium level and 10 minutes high level.

6. Quality

The following tests will be conducted with three samples each per Table 1.


Table 1: Testing Detail

Test	Test Standard	Test Condition/ Method	Pass/Fail Criteria	Additional Data to Collect for Review
Low level contact resistance (LLCR)	EIA-364-23	Subject mated specimens to 100 milliamperes maximum current and 20 millivolts maximum open circuit voltage.	10 milliohms maximum (initial) 20 milliohms maximum (final)	
Contact resistance at rated current (CRRC)	EIA-364-6	Resistance should be measured after the connector has reached thermal equilibrium, after carrying Rated load at 25°C ambient temperature.	0.5 milliohms maximum (initial and final)	
Withstanding voltage	EIA-364-20, Condition I	1000 volts AC at sea level for power contacts. 1 minute duration. Test between adjacent contacts of specimens.	No breakdown or flashover	
Durability	EIA-364-09	Mate and un-mate specimens with mating cable assembly for 50 cycles at a maximum rate of 500 cycles per hour.	LLCR before and after Post test surface wear examination: no exposed nickel or copper	
Contact Retention	EIA-364-29, Method A	15kgf pull force, both axial and at 45degrees, for a minimum of 6 seconds	No visible contact to housing displacement	N/A
Wire Retention (Parallel to the wire direction)	UL468	Pull force per wire gauge as defined in the specification	No visible contact to housing displacement	N/A
Wire Retention (perpendicular to the wire direction)	N/A	Half the pull force defined in UL 486 will be applied perpendicular to the wire direction	No visible reduction in contact to contact distance	N/A
Vibration	EIA-364-28 Test condition VII, Test condition E	15 minutes duration in each of the three mutually perpendicular direction	No discontinuities of 1 microsecond or longer duration. No plastic deformation or contact dislodging. In addition: LLCR before and after	post test contact wear optical examination, SEM/EDX optional
Shock	EIA-364-27, Method A	Subject mated specimens to 50G's half-sine shock pulses of 11 milliseconds duration. Three shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks.	No discontinuities of 1 microsecond or longer duration. No plastic deformation or contact dislodging.	post test contact wear optical examination, SEM/EDX optional

Mating Force	EIA-364-13	Measure force necessary to mate specimens at a maximum rate of 12.7 mm [.5 in] per minute.	110 N maximum per receptacle cable assembly	
Un-mating force	EIA-364-13	Measure force necessary to un-mate specimens at a maximum rate of 12.7 mm [.5 in] per minute.	15 N minimum per receptacle cable assembly	
Temperature Life	EIA-364-17, Method A, Condition 5.	Subject mated specimens to 125°C for 500 hours.	LLCR before and after	monitor contact voltage drop during test
Thermal Shock	EIA-364-32, Method A	Test condition VII: -55C to 85C for 10 cycles with 30 minute dwell time	LLCR before and after	N/A
Humidity	EIA-364-31, Class III	Subject mated specimens to 10 cycles (10days) between 25 and 65°C at 80 to 98% RH	LLCR before and after Dielectric withstand voltage before and after	N/A
Salt Spray	EIA-364-26C	Subject mated specimens to test for 48 hours, with a 5% solution salt spray, 35 +1/-2°C	LLCR before and after	N/A
Temperature rise vs. current ¹	EIA-364-70, Method 3	Attach connector to a busbar 45mm in length and heated to 85C. Stabilize at a single current level until 3 readings at 5-minute intervals are within 1°C.	Lower than 30°C	N/A

- 1) Multiple test samples may be connected in a single circuit (daisy chain) for t-rise testing. However, the current capability of jumper wires/cables connecting each test sample must be less than 125% of the target connector current. Example: the current capability of jumper wires/cables must not exceed 450A@30°C when connecting 360A@30°C test samples.

Sources for 500A ORV3 Test Busbars:



Amphenol part number 703110001
(Stepped conductor with shorting bar)

7. Regulatory

The connector shall comply with the latest edition, revision, and amendment of the following Standards:

- IEC 62368-1, Audio/video, information and communication technology equipment – Part 1: Safety requirements (applicable to meet anticipated effective date of December 20, 2020 for North America and Europe.)
- Halogen Free per JEDEC JS709C
- RoHS 2011/65/EU (RoHS 2)
- Material flammability: All materials shall be UL94 V-0 rated.
- Connectors shall be UL1977 recognized.

8. Ordering Part Numbers

Vendor	Description	P/N
Amphenol	BarKlip BK500 IO cable, screw mount	10156914-*
Staubli Electrical Connectors	Multilam ORV3 busbar connector GSR6/LA-CUD/36.4	tbd
TE Connectivity	BlackBox BB1000 OCP Rack Busbar Power Connector	2204888-1
Molex	BBC OCP ORV3 48V HARNESS ASSEMBLY	215860-XXXX

9. Revisions

Rev	Date	Author	Changes
0.00	16 Jan 2021	Skip Fry	Preliminary Draft
0.1	22 Jan 2021	Skip Fry	Revised Draft
0.2	29 Jan 2021	Skip Fry	Revised Draft
0.3	3 Feb 2021	Skip Fry	Revised Draft
0.4	18 Feb 2021	Skip Fry	Revised Draft
0.5	23 Feb 2021	Skip Fry	Revised Draft
0.6	9 Mar 2021	Skip Fry	Revised Draft
0.7	23 Mar 2021	Skip Fry	Revised Draft
0.8	9 Apr 2021	Skip Fry	Revised Panel Opening
0.9	13 Apr 2021	Skip Fry	Revised Contact Point
1.0	21 Apr 2021	Skip Fry	Revised Busbar, added Molex pn
1.1	21 Apr 2021	Skip Fry	Added chassis ground requirements
1.2	5 May 2021	Skip Fry	Added panel location dimensions
1.3	7 Jun 2021	Skip Fry	Revised Busbar tip location in Fig. 2
1.4	8 Jun 2021	Skip Fry	Revised Fig. 2 & 4, added t-rise jumper wire note and test busbar part number