



NOTES

- 1. INTERPRET DIMENSIONS PER ASME Y14.5M-2009.
- 2. ALL DIMENSIONS ARE MM.
- 3. THE MATERIALS AND MANUFACTURING METHODS USED MUST COMPLY WITH ROHS 2002/95/EC.
- 4. ALL DIMENSIONS SHOWN SHALL BE CONSIDERED CRITICAL TO FUNCTION AND CHECKED DURING FIRST ARTICLE INSPECTION.
- 5. COMPONENT SHALL BE CLEAN AND FREE FROM FOREIGN MATERIAL. DIRT,OIL,GREASE,OR OTHER CONTAMINANTS ARE NOT ALLOWED.
- 6. TOLERANCES UNLESS OTHERWISE SPECIFIED ARE:
  - HOLE TO HOLE: 0.13MM/.005IN
  - HOLE TO FOLD: 0.25MM/.01IN
  - EDGE TO FOLD: 0.25MM/.01IN
  - FOLD TO FOLD: 0.40MM/.016IN
  - HOLE TO EDGE: 0.25MM/.01IN
  - HOLE DIAMETER: 0.08/.003IN
  - ANGLES: 0.5
- 7. MATERIAL SHALL RESIST THE CREATION OF ZINC WHISKERS, SUCH AS ASTM A653 AND JIS G3302 SGOC. ELECTOGALVINIZED PLATING IS NOT ALLOWED.
- 8. ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH A BURR NO GREATER THAN 10% OF MATERIAL THICKNESS AND SHALL CONFORM TO UL SAFETY SPECIFICATION 1439.

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	INITIAL RELEASE		SM

ITEM NO.	PART NUMBER	QTY.
1	S OR2 POWER SHELF SUPPORT BRACKET 3U	1
2	S OR2 POWER SHELF SUPPORT BRACKET 3UMirror	1
3	SCREW M6X12 PAN PH TAPTITE ZN DIN7500	4

	NAME	DATE	facebook	
DRAWN	MILLS	7MAR13	TITLE: BRACKET, OR2, POWER SHELF SUPPORT, PAIR	
CHECKED				
ENG APPR.				
MFG APPR.				
PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF FACEBOOK. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF FACEBOOK IS PROHIBITED.			SIZE B	DWG. NO. 27-000401
				REV 1
			SHEET 1 OF 2	

