

NOTES: UNLESS OTHERWISE SPECIFIED.

1. INTERPRET DRAWING PER ASME Y14.100. DRAWING IS FOR INSPECTION PURPOSES ONLY. ACTUAL PART GEOMETRY IS CONTROLLED BY 3D CAD DATABASE.
2. MATERIAL: HOT-DIPPED-GALV-STEEL-SGCC
THICKNESS: 1.000±0.05mm
HARDNESS: 50-60 ROCKWELL B
SPECIFICATION: JIS G3302
PLATING/COATING: ZCS(A)X, ZINC COATING MASS: Z08, MINIMIZED SPANGLE, SKIN PASSED, CHROMATE (ANTI-FINGER PRINT) TREATED, UNOILED
MATERIAL SHALL CONTAIN 0.02% MIN TO 0.15% MAX CARBON.
3. PART WEIGHT: (0.028 GRAMS), (0.001 OZ)
4. PART SHALL BE CLEAN AND FREE OF CONTAMINANTS, METAL FLAKES, AND OIL.
5. UNDIMENSIONED 90° BENDS SHALL BE HELD AT A TOLERANCE OF ±0.5°.
- 6 ACCESSIBLE SHARP EDGES NOT PERMITTED. BURR SHALL BE TOWARDS SURFACE INDICATED. MAX BURR SIZE TO BE 10% OF MATERIAL THICKNESS AND IN COMPLIANCE WITH ULI439 STANDARD ON ALL ACCESSIBLE EDGES.

7. REFERENCE THE LATEST REVISION OF THE FOLLOWING DOCUMENTS FOR INSPECTION AND ACCEPTANCE CRITERIA:
A. MICROSOFT METAL QUALIFICATION PROCESS (D00435)
B. MICROSOFT SHEET METAL PART WORKMANSHIP STANDARDS (D00034)
C. MICROSOFT RESTRICTED SUBSTANCES FOR HARDWARE PRODUCTS (H00594)
D. MICROSOFT RESTRICTED SUBSTANCES CONTROL SYSTEM (H00642)
E. MICROSOFT PAINTED PRODUCT WORKMANSHIP AND TEST SPECIFICATION (H00388)
F. MICROSOFT SYSTEM EMC DESIGN RULES AND GUIDELINES (D00755)
G. MICROSOFT METAL STAMPING DIE MINIMUM TOOL GUIDELINES (D02520)
H. MICROSOFT METAL STAMPING DIE MAINTENANCE GUIDELINE (D02522)
- 8 THE FOLLOWING INFORMATION SHALL BE MARKED IN A PERMANENT AND LEGIBLE MANNER, LOCATED WHERE INDICATED. CHARACTERS SHALL BE A MINIMUM OF 3.0mm TALL.
A. MICROSOFT PART NUMBER
B. CURRENT REVISION
C. MANUFACTURING DATE CODE (DD MMM YYYY)
D. SUPPLIER ID (SUPPLIER ID LOCATION)
9. VENDOR SHALL SUPPLY A CERTIFICATE OF REGULATORY COMPLIANCE WITH EACH SHIPMENT THAT INCLUDES THE FOLLOWING INFORMATION:
A. NAME OF THE SUPPLIER
B. PRODUCTION DATE
C. MATERIAL MANUFACTURER'S NAME OR TRADE NAME AND MATERIAL DESIGNATION
D. NAME OF THE COMPANY BUYING THE PRODUCT
E. PART NUMBER AND REVISION
F. PURCHASE ORDER NUMBER
G. SHIPMENT DATE
H. QUANTITY OF PARTS SHIPPED
I. MANUFACTURER REPRESENTATIVE'S NAME, SIGNATURE OR FUNCTION TO ATTEST TO THE ACCURACY OF THE INFORMATION.

10. PART TOOLING IS THE PROPERTY OF MICROSOFT AND SHALL BE PERMANENTLY MARKED WITH "PROPERTY OF MICROSOFT", THE PART NUMBER, AND THE TOOL ASSET NUMBER.
11. FAI IQC/OQC FIXTURES REQUIRED AND MUST BE APPROVED BY MICROSOFT ENGINEERING. ALL DIMENSIONS ON PRINT SHALL BE INCLUDED IN FAI REPORTS. FREE STATE INSPECTION CONDITIONS REQUIRED FOR FAI. ONLY PROCESS DIMENSIONS ARE TO BE USED FOR ON-GOING PROCESS CONTROL PER MICROSOFT METAL QUALIFICATION PROCESS (D00435). ON-GOING PROCESS CONTROL INSPECTIONS SHALL BE DONE IN FREE STATE. DIMENSIONS THAT ARE DRIVEN BY ASSEMBLY LEVEL TOLERANCE CHAIN STUDIES ARE INDICATED WITH A (★) SYMBOL.

12. PARTS SHALL BE PACKAGED FOR SUPPLIER INTERNAL DISTRIBUTION.


- 13 COIN EDGES WHERE INDICATED TO REMOVE SHARP EDGES. BREAKS IN COINING FOR CARRYING WEBS REQUIRE APPROVAL OF MICROSOFT ENGINEERING.

14. BEND RADII AND RELIEFS SHALL COMPLY TO ELECTRONIC DATABASE.

15. CARRY POINTS SHALL BE RECESSED BY 0.25mm MAX. ANY DEVIATION REQUIRES APPROVAL BY MICROSOFT ENGINEERING.

16. TOLERANCE KEY FOR NON-DIMENSIONED ITEMS:
HOLE DIAMETER: ±0.08
HOLE TO HOLE: ±0.13
HOLE TO EDGE: ±0.13
EDGE TO EDGE: ±0.13
HOLE TO BEND: ±0.13
EDGE TO BEND: ±0.21
BEND TO BEND: ±0.26
EMBOSS DEPTH: ±0.26
ANGLE: ±0.5°

17. DIMENSIONS AND TOLERANCES NOT MARKED CRITICAL, TOOLING OR PROCESS SHALL BE CONSIDERED REFERENCE DIMENSIONS. ONLY CRITICAL, TOOLING AND PROCESS DIMENSIONS ARE REQUIRED TO BE COMPLIANT FOR FAI. ADDITIONAL MEAUREMENTS REQUIRED AT ENGINEERING REQUEST.



DIMENSIONS ARE IN MILLIMETERS			-	-
GENERAL TOLERANCES			SEE NOTES	SEE NOTES
STD. DIM	SEE NOTES	SEE NOTES	DOCUMENT NO	GENERAL DESCRIPTION
ANGLE	SEE NOTES	SEE NOTES	APPLICABLE SPECIFICATION TABLE	
RADIUS	SEE NOTES	SEE NOTES	THIS DOCUMENT AND THE INFORMATION CONTAINED HEREIN ARE PROPRIETARY TO MICROSOFT CORPORATION AND SHALL NOT BE USED BY, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE OUTSIDE OF MICROSOFT CORPORATION WITHOUT THE PRIOR WRITTEN PERMISSION OF MICROSOFT CORPORATION.	

DRAWN PENSAR	DATE 11/5/13
CHECKED -	DATE -
ENGINEER BRUBEN	DATE 11/5/13
ENGINEER -	DATE -
COG ENGR -	DATE -
MFG ENGR -	DATE -
TOOLING -	DATE -
QUALITY -	DATE -
RELEASED -	DATE -

Microsoft	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: MILLIMETERS TOLERANCES ARE: SEE TOLERANCE BLOCK	
DO NOT SCALE DRAWING	
LEGEND: ★ = TOLERANCE CHAIN DIM □ = CRITICAL DIM ○ = TOOLING DIM △ = PROCESS DIM Ⓢ = DIMENSION ID	

MS PART NO: X887752-001 MS PDM VER: C.1		TITLE: STAMPING, BULKHEAD BLANK	
SIZE: D	THIRD ANGLE PROJECTION 	DRAWING NO: X887752	REV: C
SCALE: 1.5:1		SHEET: 1 OF 2	

D

C

B

A

D

C

B

A

Microsoft®

MS PART NO: X887752-001
MS PDM VER: C.1

TITLE:

STAMPING, BULKHEAD BLANK

SIZE:

THIRD ANGLE PROJECTION

DRAWING NO:

REV:

D



X887752

C

SCALE:

SHEET:

2:1

2 OF 2

8

7

6

5

4

3

2

1

8

7

6

5

4

3

2

1