



NOTES UNLESS OTHERWISE SPECIFIED:

1. INTERPRET DRAWING PER ASME Y14.100. DRAWING IS FOR INSPECTION PURPOSES ONLY. ACTUAL PART GEOMETRY IS CONTROLLED BY 3D CAD DATABASE.
2. MATERIAL: HOT-DIPPED-GALV-STEEL-SGCC
THICKNESS: 0.800±0.1mm
HARDNESS: 50-60 ROCKWELL B
SPECIFICATION: JIS G3302
PLATING/COATING: ZCS(A)X, ZINC COATING MASS: Z08, MINIMIZED SPANGLE, SKIN PASSED, CHROMATE (ANTI-FINGER PRINT) TREATED, UNOILED
MATERIAL SHALL CONTAIN 0.02% MIN TO 0.15% MAX CARBON.
3. PART WEIGHT: (131.168 GRAMS), (4.628 OZ)
4. PART SHALL BE CLEAN AND FREE OF CONTAMINANTS, METAL FLAKES, AND OIL.
- 5 AS DIMENSIONED OR Ø3.60. STANDARD TOLERANCE APPLIES.
- 6 ACCESSIBLE SHARP EDGES NOT PERMITTED. BURR SHALL BE TOWARDS SURFACE INDICATED. MAX BURR SIZE TO BE 10% OF MATERIAL THICKNESS AND IN COMPLIANCE WITH ULI439 STANDARD ON ALL ACCESSIBLE EDGES.
7. REFERENCE THE LATEST REVISION OF THE FOLLOWING DOCUMENTS FOR INSPECTION AND ACCEPTANCE CRITERIA:
A. MICROSOFT METAL QUALIFICATION PROCESS (D00435)
B. MICROSOFT SHEET METAL PART WORKMANSHIP STANDARDS (D00034)
C. MICROSOFT RESTRICTED SUBSTANCES FOR HARDWARE PRODUCTS (H00594)
D. MICROSOFT RESTRICTED SUBSTANCES CONTROL SYSTEM (H00642)
E. MICROSOFT PAINTED PRODUCT WORKMANSHIP AND TEST SPECIFICATION (H00388)
F. MICROSOFT SYSTEM EMC DESIGN RULES AND GUIDELINES (D00755)
G. MICROSOFT METAL STAMPING DIE MINIMUM TOOL GUIDELINES (D02520)
H. MICROSOFT METAL STAMPING DIE MAINTENANCE GUIDELINE (D02522)
- 8 THE FOLLOWING INFORMATION SHALL BE MARKED IN A PERMANENT AND LEGIBLE MANNER, LOCATED WHERE INDICATED. CHARACTERS SHALL BE A MINIMUM OF 3.0mm TALL.
A. MICROSOFT PART NUMBER
B. CURRENT REVISION
C. MANUFACTURING DATE CODE (DD MMM YYYY)
D. SUPPLIER ID (SUPPLIER ID LOCATION)
9. VENDOR SHALL SUPPLY A CERTIFICATE OF REGULATORY COMPLIANCE WITH EACH SHIPMENT THAT INCLUDES THE FOLLOWING INFORMATION:
A. NAME OF THE SUPPLIER
B. PRODUCTION DATE
C. MATERIAL MANUFACTURER'S NAME OR TRADE NAME AND MATERIAL DESIGNATION
D. NAME OF THE COMPANY BUYING THE PRODUCT
E. PART NUMBER AND REVISION
F. PURCHASE ORDER NUMBER
G. SHIPMENT DATE
H. QUANTITY OF PARTS SHIPPED
I. MANUFACTURER REPRESENTATIVE'S NAME, SIGNATURE OR FUNCTION TO ATTEST TO THE ACCURACY OF THE INFORMATION.
10. PART TOOLING IS THE PROPERTY OF MICROSOFT AND SHALL BE PERMANENTLY MARKED WITH "PROPERTY OF MICROSOFT", THE PART NUMBER, AND THE TOOL ASSET NUMBER.
11. FAI IQC/OQC FIXTURES REQUIRED AND MUST BE APPROVED BY MICROSOFT ENGINEERING. FREE STATE INSPECTION CONDITIONS REQUIRED FOR FAI. ON-GOING PROCESS CONTROL INSPECTIONS SHALL BE DONE IN FREE STATE.
12. PARTS SHALL BE PACKAGED FOR SUPPLIER INTERNAL DISTRIBUTION.
- 13 COIN EDGES WHERE INDICATED TO REMOVE SHARP EDGES. BREAKS IN COINING FOR CARRYING WEBS REQUIRE APPROVAL OF MICROSOFT ENGINEERING.
14. BEND RADIUS AND RELIEFS SHALL COMPLY TO ELECTRONIC DATABASE.
15. CARRY POINTS SHALL BE RECESSED BY 0.25mm MAX. TOOLING HOLES OR OTHER DEVIATIONS REQUIRE APPROVAL BY MICROSOFT ENGINEERING.
16. TOLERANCE KEY FOR NON-DIMENSIONED ITEMS:
HOLE DIAMETER: PUNCH DIRECTION ±0.08
CHAMFERED HOLE DIAMETER: BURR SIDE ±0.15
HOLE TO HOLE: ±0.13
HOLE TO EDGE: ±0.13
EDGE TO EDGE: ±0.13
HOLE TO BEND: ±0.13
EDGE TO BEND: ±0.21
BEND TO BEND: ±0.26
EMBOSS DEPTH: ±0.26
ANGLE: ±0.5°
17. VENDOR MODIFICATION OF HOLE FEATURE SIZING AND TOLERANCES FOR PRESS-IN HARDWARE IS ALLOWED FOR VENDOR SPECIFIC HARDWARE PER MICROSOFT APPROVAL.

18. DIMENSIONS AND TOLERANCES NOT MARKED CRITICAL, TOOLING OR PROCESS SHALL BE CONSIDERED REFERENCE DIMENSIONS. ONLY CRITICAL, TOOLING AND PROCESS DIMENSIONS ARE REQUIRED TO BE COMPLIANT FOR FAI. ADDITIONAL MEAUREMENTS REQUIRED AT ENGINEERING REQUEST.

REV	ECO NO	DESCRIPTION	DRAWN	APVD DATE
A	-	INITIAL RELEASE	PENSAR	11/6/13
B	-	DFM FEEDBACK CHANGES. ADDED HEM CUTOUT IN CORNER	BROILI	1/22/14
C	-	UPDATED NOTE 1, ADDED NOTE 18	N. TOLCHIN	5/15/14
D	-	TITLE WAS: PSU DIVIDER LES.	G. HAZEN	07/25/14




DIMENSIONS ARE IN MILLIMETERS			
GENERAL TOLERANCES			
	X	X.X	X.XX
STD. DIM	SEE NOTES		
ANGLE	SEE NOTES		
RADIUS	SEE NOTES		

DOCUMENT NO	GENERAL DESCRIPTION
APPLICABLE SPECIFICATION TABLE	THIS DOCUMENT AND THE INFORMATION CONTAINED HEREIN ARE PROPRIETARY TO MICROSOFT CORPORATION AND SHALL NOT BE USED BY, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE OUTSIDE OF MICROSOFT CORPORATION WITHOUT THE PRIOR WRITTEN PERMISSION OF MICROSOFT CORPORATION.

DRAWN PENSAR	DATE 11/1/13
CHECKED -	DATE -
ENGINEER PENSAR	DATE 11/1/13
ENGINEER -	DATE -
COG ENGR -	DATE -
MFG ENGR -	DATE -
TOOLING -	DATE -
QUALITY -	DATE -
RELEASED -	DATE -

Microsoft		MS PART NO: X890862-001 MS PDM VER: D.1	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: MILLIMETERS TOLERANCES ARE: SEE TOLERANCE BLOCK		TITLE: PSU DIVIDER LFF	
DO NOT SCALE DRAWING		SIZE: D	THIRD ANGLE PROJECTION
LEGEND: ★ = TOLERANCE CHAIN DIM ■ = CRITICAL DIM ○ = TOOLING DIM △ = PROCESS DIM Ⓢ = DIMENSION ID		DRAWING NO: X890862	REV: D
		SCALE: 1.000	SHEET: 1 OF 4



REVISIONS	ECO NO.	DESCRIPTION	DRAWN	APPROVED
SEE SHEET 1 FOR REVISIONS				

Microsoft® MS PART NO: X890862-001
MS PDM VER: D.1

TITLE:
PSU DIVIDER LFF

SIZE: D	THIRD ANGLE PROJECTION	DRAWING NO: X890862	REV: D
SCALE: 1.500		SHEET: 2 OF 4	

8

7

6

5

4

3

2

1

REVISIONS


ECO NO.

DESCRIPTION

DRAWN

APPROVED

SEE SHEET 1 FOR REVISIONS




FLAT PATTERN VIEW

MicrosoftMS PART NO: X890862-001
MS PDM VER: D.1

TITLE:

PSU DIVIDER LFF

SIZE:

DTHIRD ANGLE
PROJECTION

DRAWING NO:

X890862SCALE:
1.000

REV:

D

SHEET:

3 OF 4

