



NOTES:(UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :SGCC ; T=1.0±5%
2. BREAK ALL SHARP CORNERS AND EDGES.  
ALL SURFACES AND EDGES TO BE ADEQUATE FOR SAFE HANDLING PER UL SAFETY SPECIFICATION 1439.
3. FINISH:POWDER PAINT PER PANTONE PMS 433U
4. INSIDE SURFACE TO BE FREE OF PAINT
5. THE OUTSIDE OF THE CHASSIS IS REQUIRED PAINTING/COATING EXCEPT AREA
6. MATERIAL OF STAND OFF : Free Cutting Steel , ZINC PLATED
7. FORBID TO PAINT : THE TOP END OF STAND OFF
- 8.TOLERANCES: BEND TO BEND:±0.25mm  
EDGE TO BEND:±0.15mm  
SLOT TO BEND:±0.15mm  
SLOT TO SLOT:±0.10mm  
SLOT TO EDGE:±0.10mm  
EDGE TO EDGE:±0.10mm
9. 尺寸標註旁有▲符號者，為特定之重點尺寸
10. 尺寸標註旁有 CTQ 符號者，為 CTQ 尺寸
11. MUST MEET DELTA SPEC :10000-0002 & 10000-0094 & 10000-0162.

NET16-2126400A

<b>AGEMA SYSTEMS, INC.</b>			DIMENSIONAL TOLERANCES					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF AGEMA SYSTEMS. AND SHALL NOT BE REPRODUCED OR USED AS THE BASIS FOR THE MANUFACTURE OR SELL OF APPARATUSES OR DEVICES WITHOUT PERMISSION .			( ) ( ) ( ) ( ) ( )					
DRN BY	STEVEN WANG	11/06/'16	0 ~ 25	±0.02	±0.05	±0.1	±0.2	±0.4
DSN BY			26 ~ 80	±0.05	±0.08	±0.15	±0.3	±0.8
CKD BY	ALLEN YANG	11/06/'16	81 ~ 200	±0.08	±0.12	±0.25	±0.5	±1.0
PART NAME	CASE COVER		201 ~ 400	±0.12	±0.2	±0.3	±1.0	±2.0
USED ON	AG7648C-R(AGEMA)		401 ~	±0.2	±0.3	±0.4	±1.5	±4.0
			PART NO.	3991233803				
			UNIT:	mm				REV.
			SCALE:	NONE				03
			ANGULAR:	DEG	1	OF	1	