





REVISIONS						
REV.	DESCRIPTION	MOD BY	MOD DATE	APPROVED	APPROVED DATE	
01	INITIAL RELEASE					



1. DIMENSION ARE IN MILIMETER
2. MATERIAL: 0.8mm CRS
3. TOLERANCE UNLESS OTHERWISE SPECIFIED: ±0.25mm, MAX BEND RADIUS 0.30mm
4. THE FOLLOWING DIMENSIONS MUST MEET A Cp>=1.33 and CpK>=1.00
5. BEND RELIEFS ALLOWED. FACEPLATE GEOMETRY MUST BE MAINTAINED. ANY DEVIATIONS MUST BE APPROVED.
6. PARTS MUST COMPLY WITH RoHS DIRECTIVE 2002/95/EC. FURTHERMORE, THE USE OF HEXAVALENT CHROMIUM IN THE FABRICATION PROCESS IS NOT ALLOWED.

UNLESS OTHERWISE SPECIFIED: 1. DIMENSIONS ARE IN: MILIMETER 2. DO NOT SCALE DRAWING. 3. TOLERANCES: ANGLES ± 1.0° XX ± 0.25			SIGNATURE DRAWN BY: J. MAI CHECKED BY: J. HELD ENGR APVD:	DATE 3/03/2019 3/03/2019	OPEN TITLE: DOCUMENT NUMBER NIC_OCPv3_SFF_Faceplate_Pulltab_20190303		SIZE D	SCALE 3:1	SHEET 1 OF 1	REV 01
---	--	--	---	--------------------------------	---	--	-----------	--------------	-----------------	-----------