


REVISIONS						
REV.	DESCRIPTION	MOD BY	MOD DATE	APPROVED	APPROVED DATE	
01	INITIAL RELEASE					



1. DIMENSION ARE IN MILIMETER
2. MATERIAL: 0.8mm CRS
3. TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0.25\text{mm}$, MAX BEND RADIUS 0.30mm
4. THE FOLLOWING DIMENSIONS MUST MEET A $C_p \geq 1.33$ and $C_{pK} \geq 1.00$
5. BEND RELIEFS ALLOWED. FACEPLATE GEOMETRY MUST BE MAINTAINED. ANY DEVIATIONS MUST BE APPROVED.
6. PARTS MUST COMPLY WITH RoHS DIRECTIVE 2002/95/EC. FURTHERMORE, THE USE OF HEXAVALENT CHROMIUM IN THE FABRICATION PROCESS IS NOT ALLOWED.

UNLESS OTHERWISE SPECIFIED:		SIGNATURE		DATE		OPEN	
1. DIMENSIONS ARE IN: MILIMETER		DRAWN BY: J. MAI		3/03/2019		TITLE:	
2. DO NOT SCALE DRAWING.		CHECKED BY: J. HELD		3/03/2019		DOCUMENT NUMBER	
3. TOLERANCES:		APVD:				NIC_OCPv3_LFF_Faceplate_Latch_20190303	
ANGLES $\pm 1.0^\circ$		THIRD ANGLE PROJECTION				SIZE	
XX ± 0.25						SCALE	
						SHEET	
						1 OF 1	
						REV	
						01	