



REVISIONS						
REV.	DESCRIPTION	MOD BY	MOD DATE	APPROVED	APPROVED DATE	
01	INITIAL RELEASE					



1. DIMENSION ARE IN MILIMETER
2. MATERIAL: 0.8mm CRS
3. TOLERANCE UNLESS OTHERWISE SPECIFIED: ± 0.25mm, MAX BEND RADIUS 0.30mm
4. TOLERANCE SUPPORTS ASSEMBLY CTF'S. OTHER COMBINATIONS OF TOLERANCES ARE ALSO POSSIBLE TO MEET CTF'S.
5. BEND RELIEFS ALLOWED. FACEPLATE GEOMETRY MUST BE MAINTAINED. ANY DEVIATIONS MUST BE APPROVED.
6. PARTS MUST COMPLY WITH RoHS DIRECTIVE 2002/95/EC. FURTHERMORE, THE USE OF HEXAVALENT CHROMIUM IN THE FABRICATION PROCESS IS NOT ALLOWED.



SAME ON OPPOSITE SIDE OF FACEPLATE

UNLESS OTHERWISE SPECIFIED:		SIGNATURE		DATE		OCP NIC 3.0	
1. DIMENSIONS ARE IN: MILIMETER		DRAWN BY: J. MAI		12/05/2019		OPEN	
2. DO NOT SCALE DRAWING.		CHECKED BY: J. HELD		12/05/2019		TITLE:	
3. TOLERANCES:		ENGR		APVD:		DOCUMENT NUMBER	
ANGLES: ± 1.0°		THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		NIC_OCPv3_LFF_Faceplate_Latch_20191205	
XX ± 0.25		SIZE		SCALE		SHEET	
		D		3:1		1 OF 1	
						REV	
						01	