


- NOTES:
- 1. QUALITY CONTROL DIMENSIONS SPECIFIED AS (1)-(4).
 - 2. REMOVE ALL OIL, BURRS, BREAK, SHARP EDGES AND CORNERS.
 - 3. ALL MATERIALS USED IN THE CONSTRUCTION OF THIS PART (INCLUDING RAW STOCK, COATING, HARDWARE, GASKETING, ETC.) MUST BE RoSH COMPLIANT.
 - 4. NON-SHOWN DIMENSION IN THE DRAWING, MUST BE TAKEN FROM 3D DATA.
 - 5. AFTER ASSEMBLING, THE LOW MATERIAL WITHOUT PAINT CAN NOT BE EXPOSED.
 - 6. NO OVERSPRAY ALLOWED.
 - 7. THIS PART SHOULD MATCH WELL WITH Base 123100000908A.

Reason	.	.	UNSPECIFIED TOL 'S (+/-0.2mm)								 FINISH.		Accton TECHNOLOGY CORP.							
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.	.	.	ANGLE +/- 1°	GRADE		0	1	2	3	4	5	Non-painting								
	.	.		DIM	PART NO. 123700000110A								SCALE 0.500	UNIT [IN]						
	.	.		ROUGHNESS	0-----16		0.05	0.1	0.15	0.2	0.2	0.3	DESIGN Kevin Ke Jan-11-16							
	.	.			16-----63		0.050	0.15	0.2	0.3	0.3	0.5								
	.	.			63-----250		0.05	0.2	0.25	0.4	0.5	1.2								
AI	Modify the dimensions			250-----500		0.1	0.25	0.3	0.5	0.8	1.8	MATERIAL SECC, t=0.6mm		DWG. TITLE. SHEET 1/1 REV. SIZE						
ZONE	DESCRIPTION			500-----1000		0.3	0.5	0.8	1.2	3.0			Air Baffle-L ES5654BQ-1115-168ZZ A1 A3							