


- NOTES:
- 1.QUALITY CONTROL DIMENSIONS SPECIFIED AS (1)~(3).
  - 2.REMOVE ALL OIL,BURRS,BREAK,SHARP EDGES AND CORNERS.
  - 3.ALL MATERIALS USED IN THE CONSTRUCTION OF THIS PART (INCLUDING RAW STOCK, COATING, HARDWARE, GASKETING, ETC.) MUST BE RoSH COMPLIANT.
  - 4.NON-SHOWN DIMENSION IN THE DRAWING,MUST BE TAKEN FROM 3D DATA.
  - 5.AFTER ASSEMBLING,THE LOW MATERIAL WITHOUT PAINT CAN NOT BE EXPOSED.
  - 6.NO OVERSPRAY ALLOWED.
  - 7.THIS PART SHOULD MATCH WELL WITH Base 123100000908A

Reason	.	.	UNSPECIFIED TOL 'S (+/-0.2mm)							 FINISH.		Accton TECHNOLOGY CORP.							
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.	.	.	ANGLE +/- 1°	DIM	GRADE					Non-painting									
	.	.			0	1	2	3	4	5	PART NO. 123700000111A						SCALE0.500	UNIT MM [IN]	
	.	.			ROUGHNESS		16-----63	0.050	0.15	0.2		0.3	0.3	0.8					
	.	.			63-----250	0.05	0.2	0.25	0.4	0.5		1.2							
	.	.			250-----500	0.1	0.25	0.3	0.6	0.8		1.8							
					500-----1000	0.3	0.5	0.8	1.2	3.0	MATERIAL SECC, t=0.5mm	DESIGNKevin Ke	Jan-11-16	DWG. TITLE.	SHEET 1/1	REV.	SIZE		
ZONE		DESCRIPTION																Air Duct ES5654BQ-1115-168ZZ	A0