



# Open CloudServer – vNext

Aug 30, 2016

Mark Shaw

Microsoft Cloud + Enterprise



# Open CloudServer vNext Goals for OCP

## Standardization of OCP motherboard

- Reduce fragmentation within OCP community
- Supports side-by-side high-performance CPUs up to 200W
- BOM and Firmware minimization for robust qualification

## Flexible, Modular Design for use across OCP

- Adaptable to different server node chassis designs and racks
- Different Data Center environmental and usage models

## Agility to adapt to new technologies

- Larger form factor, more I/O slots more adaptable

## Cost Reduction across full lifecycle

- Lowest bare bones costs for empty chassis cost and transportation
- Lower solution costs

# OCP Components





# OCS vNext



# Choose the components you need


Motherboard




OCS vNext



Open Rack



EIA 19"



Other 19"/21"



# OCS vNext – Components

42U & 48U  
1200mm EIA Rack

**Motherboard**


Management GbE

Server Blade

88 HDD JBOD

Rack Management

World-wide  
Power  
Solution



# Motherboard

## Optimized for Performance, I/O flexibility


- High-performance CPUs, up to 32 DIMMs
- Three Standard PCI-Express Gen3 slots
  - OCP Mezzanine on card carrier
- Eight to 16 CloudSSD M.2 NVMe Flash cards

## Management flexible to meet your needs

- BMC Gigabit Ethernet (Redfish or IPMI)
- NCSI side-band through OCP Mezz
- KVM enabled on motherboard


## Power and Thermal

- Cabled power connector adapts to the chassis
- Side-by-side CPUs for lower fan power



# OCS vNext – Components

42U & 48U  
1200mm EIA Rack



# Server Blade

## Front Cabled I/O and Cold Aisle Service


- Three PCIe x16 slots
- Blind mate rear power and management
- Latching at the chassis, pull to release

## CloudSSD Optimized Storage

- Eight to 16 CloudSSD M.2 NVMe Flash slots
- LFF and SFF slots intended for low-cost boot drives

## Embedded PSU and Fans


- 750W PSU: Dual-feed, three-phase, N+1 high availability solution
- Six N+2 fans for high-availability, lower per rack CFM
- Customized high-performance vapor chamber remote heatsink





# OCS vNext – Components


42U & 48U  
1200mm EIA Rack



# 750W High Availability Power Supply

## Three x 375 PSUs Fully Integrated


- N+1 HA → no repair on failure
- Dual-feed auto-selection (IVS)
- Three-phase balanced AC power




## Fault Mode Resiliency

- AC feed failure, automatic fail over
- PSU failure throttles if necessary
- Double fault will be extremely rare


Normal mode  
750W



Fault mode  
750W



# OCS vNext – Components



# World-Wide Power Solution

## Supports high availability data centers

- Dual-feed, three-phase Power to every slot
- Rack power monitoring and throttling

## Power and Management Distribution Unit (PMDU)


- Distributes power and management
- Integrated Rack Manager
- Supports blind-mate servers

## AC “7-Wire” Adapter for world-wide deployments

- Three phases plus ground return
- Data Center whips under development
  - 208V-50A, 415V-30A, 400V-32A



# OCS vNext – Components



# Management Architecture

## Rack Management


- Restful API I/F – i.e. Redfish via external Ethernet
- Rack Manager (RM) ARM CPU running Linux

## Blade Management flexible to your needs


- GbE I/F to each blade's BMC
- NCSI enabled on motherboard with cable to OpenRack Mezz Carrier
- KVM enabled on motherboard

## Deployments

- Integrated into PMDU for rack scale deployments
- Standalone version for hardware that does not use the PMDU



# OCS vNext – Components



# JBOD – High Density Storage

## 4U JBOD – 88 HDDs / chassis


- Drawer design – slide out for repair
- Hot-plug HDDs, front-serviceable expanders
- Front cabled to compute blade head-node

## Robust Feature Set


- BMC gathers HDD temps and status info
- Individual HDD on/off to minimize NTF

## Configuration

- One OCS vNext head node, 88 HDD each
- Two OCS vNext head nodes, 44 HDD each
- Four OCS vNext head nodes, 22 HDD each



4U JBOD





# OCS vNext – Components

## 42U & 48U EIA 19" Rack

